




# INSERTS



# INSERTS

## System, compatibility and choice

System means order and clarity. But order means different things to different people. That's why storage solutions must possess both system - and choice. All raaco product ranges have both.

The flexibility and choice don't just exist within the individual systems, but also between them. The inserts ensure many combinations between the Assorter Boxes in A4, A5 and A6 size, Pocketboxes, CarryLites, Boxxser, Compact, ToolCase and the 250-3 drawers for cabinets.


The wide range of inserts ensures that you can customise your raaco product to suit particular requirements - and just as easily move it again. The inserts and the content stay in place thanks to a special installation system, which also makes even the smallest items easy to get hold of.

### Inserts series 55 - height 47 mm




**A9-1**

39 x 55 mm




**A9-2**

39 x 109 mm



**A9-3**

39 x 163 mm




**A9-4**

39 x 218 mm




**A8-1**

55 x 79 mm




**A8-2**

55 x 157 mm




**A8-3**

55 x 235 mm




**A7-1**

79 x 109 mm



**A7-2**


79 x 218 mm



**A6-1**


109 x 157 mm

### Inserts series 80 - height 69 mm




**BA8-1**

55 x 79 mm




**BA8-2**

55 x 157 mm




**BA8-3**

55 x 235 mm




**BA7-1**

79 x 109 mm



**BA7-2**


79 x 218 mm



**BA6-1**


109 x 157 mm

### Inserts series 27 - height 24 mm




**A71**

79 x 109 mm




**A73**

79 x 109 mm



**A75**



79 x 109 mm




**A78**

79 x 109 mm


# BOXXSER 55 4x4




## Inserts series 55




**A9-1**




**A9-2**




**A9-3**




**A9-4**




**A8-1**




**A8-2**



**A7-1**




**A7-2**




**A6-1**


## Inserts series 27




**A71**



**A73**





**A75**




**A78**

Notice that the O-profiles in the lid of the Boxxser only fits tightly when insert A71 is placed on top of the half inserts.


# BOXXSER 55 5x5




## Inserts series 55




**A9-1**




**A9-2**




**A9-3**




**A9-4**




**A8-1**




**A8-2**



**A7-1**




**A7-2**




**A6-1**


## Inserts series 27




**A71**



**A73**





**A75**




**A78**

Notice that the O-profiles in the lid of the Boxxser only fits tightly when insert A71 is placed on top of the half inserts.


# BOXXSER 55 6x6




## Inserts series 55




**A9-1**




**A9-2**




**A9-3**




**A9-4**




**A8-1**




**A8-2**




**A8-3**



**A7-1**




**A7-2**




**A6-1**


## Inserts series 27




**A71**



**A73**





**A75**




**A78**

Notice that the O-profiles in the lid of the Boxxser only fits tightly when insert A71 is placed on top of the half inserts.


# BOXXSER 55 5x10




## Inserts series 55




A9-1




A9-2




A9-3




A9-4




A8-1




A8-2




A8-3



A7-1




A7-2




A6-1


## Inserts series 27




A71



A73





A75




A78

Notice that the O-profiles in the lid of the Boxxser only fits tightly when insert A71 is placed on top of the half inserts.


# BOXXSER 80 5x10




## Inserts series 80




**BA8-1**




**BA8-2**




**BA8-3**



**BA7-1**




**BA7-2**




**BA6-1**


## Inserts series 27




**A71**



**A73**





**A75**




**A78**

Notice that the O-profiles in the lid of the Boxxser only fits tightly when insert A71 is placed on top of the half inserts.


# BOXXSER 80 8x8




## Inserts series 80




**BA8-1**




**BA8-2**




**BA8-3**



**BA7-1**




**BA7-2**




**BA6-1**


## Inserts series 27




**A71**



**A73**



**A75**



**A78**

Notice that the O-profiles in the lid of the Boxxser only fits tightly when insert A71 is placed on top of the half inserts.